

## Product data sheet

### Characteristics

# EY56E4

## Enclosure, Easy56, 4 Gang



### Main

Product name	Easy56
Product or component type	Back box
Device short name	EY56E4

### Complementary

Material	PVC (polyvinyl chloride): housing
Device mounting	Surface
Mounting mode	Wall-mounted
Net weight	0.695 kg
Base dimension	198 x 198 mm
Height	198 mm
Width	198 mm
Depth	63 mm
Colour	Grey (RAL 7035)




### Environment

Standards	AS 3100
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.5 cm
Package 1 Width	7.3 cm
Package 1 Length	20.5 cm
Package 1 Weight	730.0 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

