

## Product data sheet

### Characteristics

# EY56P320

## Easy56, Plug, 3 Pin, 20A, 250V



### Main

Product name	Easy56
Product or component type	Plug
Device short name	EY56P320
Plug, socket category	Low voltage
Poles description	1P + N + E
Pin number	3 pins
Shape of pin	Tubular
Outlet standard	Australian/New Zealand

### Complementary

Plug, socket, control station shape	Straight
[In] rated current	20 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50 Hz
Material	Polycarbonate: housing
Contacts material	Pins: brass
Connections - terminals	Screw terminals
Cable cross section	1...4 mm <sup>2</sup>
Cable outer diameter	7...16 mm
Wire stripping length	10...35 mm
Cable entry	Cable gland
Net weight	0.298 kg
Height	78 mm
Width	78 mm
Depth	152 mm
Colour	Plug: orange (RAL 2004) Body: clear

### Environment

Standards	AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	9.6 cm
Package 1 Length	17.2 cm
Package 1 Weight	336.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>