

Product data sheet

Characteristics

EY56P410

Plug, Easy56, 4 Pin, 10A, 500V

Main

Product name	Easy56
Product or component type	Plug
Device short name	EY56P410
Plug, socket category	Low voltage
Poles description	3P + E
Pin number	4 pins
Shape of pin	Tubular
Outlet standard deviation	Australian/New Zealand

Complementary

Plug, socket, control station shape	Straight
[In] rated current	10 A
[Ue] rated operational voltage	500 V
Network type	AC
Network frequency	50 Hz
Material	Polycarbonate: housing
Contacts material	Pins: brass
Connections - terminals	Screw terminals
Cable cross section	1...4 mm ²
Cable outer diameter	7...16 mm
Wire stripping length	10...35 mm
Cable entry	Cable gland
Net weight	0.298 kg
Height	78 mm
Width	78 mm
Depth	152 mm
Colour	Plug: orange (RAL 2004) Body: clear

Environment

Standards	AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.0 cm
Package 1 Width	8.0 cm
Package 1 Length	9.5 cm
Package 1 Weight	313.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes