

## Product data sheet

### Characteristics

# EY56P510

## Easy56 Plug - 5 Pin - 10A - 500V



### Main

Product name	Easy56
Product or component type	Plug
Device short name	EY56P510
Plug, socket category	Low voltage
Poles description	3P + N + E
Pin number	5 pins
Shape of pin	Tubular
Outlet standard	Australian/New Zealand

### Complementary

Plug, socket, control station shape	Straight
[In] rated current	10 A
[Ue] rated operational voltage	500 V
Network type	AC
Network frequency	50 Hz
Material	Polycarbonate: housing
Contacts material	Pins: brass
Connections - terminals	Screw terminals
Cable cross section	1...4 mm <sup>2</sup>
Cable outer diameter	7...16 mm
Wire stripping length	10...35 mm
Cable entry	Cable gland
Net weight	0.298 kg
Height	78 mm
Width	78 mm
Depth	152 mm
Colour	Plug: orange (RAL 2004) Body: clear

### Environment

Standards	AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

### Packing Units

Package 1 Weight	362.000 g
Package 1 Height	82.000 mm
Package 1 width	95.000 mm
Package 1 Length	171.000 mm

