

## Product data sheet

### Characteristics

# EY56SO310LE

Easy56, Socket, 3 Pin, 10A, 250V, Less Enclosure



### Main

Product name	Easy56
Product or component type	Socket-outlet
Device short name	EY56SO310LE
Plug, socket category	Low voltage
Poles description	1P + N + E
Network type	AC
Outlet standard	Australian/New Zealand

### Complementary

Mounting mode	Surface mounted
Plug, socket, control station shape	Straight
[In] rated current	10 A
Pin number	3 pins
Shape of pin	Flat
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals 1.5...6 mm <sup>2</sup> rigid or stranded cable
Wire stripping length	10 mm
Net weight	0.216 kg
Height	101 mm
Width	101 mm
Depth	65 mm
Colour	Grey (RAL 7035)

### Environment

Standards	AS/NZS 3112
Quality labels	RCM
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	10.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	217.0 g

