

Product data sheet

Characteristics

EY56SO315

Easy56 Socket - 3 Pin - 15A - 250V



Main

Product name	Easy56
Product or component type	Socket-outlet
Device short name	EY56SO315
Plug, socket category	Low voltage
Poles description	1P + N + E
Network type	AC
Outlet standard	Australian/New Zealand

Complementary

Mounting mode	Surface mounted
Plug, socket, control station shape	Straight
[In] rated current	15 A
Pin number	3 pins
Shape of pin	Flat
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals 1.5...6 mm ² rigid or stranded cable
Wire stripping length	10 mm
Product weight	0.471 kg
Height	101 mm
Width	101 mm
Depth	101 mm
Colour	Grey (RAL 7035)

Environment

Standards	AS/NZS 3112
Quality labels	RCM
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

Packing Units

Package 1 Weight	434.600 g
Package 1 Height	115.000 mm
Package 1 width	105.000 mm
Package 1 Length	105.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------