

Product data sheet

Characteristics

EY56SW110

Easy56, Switch, 1P, 10A, 250V



Main

Product name	Easy56
Device short name	EY56SW110
Product or component type	Switch
Poles description	1P
Control type	Rotary knob
Rotary handle padlocking	2 padlocks 8 mm

Complementary

[Ue] rated operational voltage	250 V AC 50 Hz
[Ithe] conventional enclosed thermal current	10 A
[Ie] rated operational current	10 A
Connections - terminals	Screw terminals cable(s) 1.5...6 mm ² rigid or stranded
Height	101 mm
Width	101 mm
Depth	101 mm
Net weight	0.471 kg
Colour	Body: grey (RAL 7035) Rotary handle: dark grey




Environment

Standards	AS/NZS 3133
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	10.4 cm
Package 1 Length	10.6 cm
Package 1 Weight	495.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
