

## Product data sheet

### Characteristics

# EY56SW110

## Easy56 Switch - 1P - 10A - 250V



### Main

Product name	Easy56
Device short name	EY56SW110
Product or component type	Switch
Poles description	1P
Control type	Rotary knob
Rotary handle padlocking	2 padlocks 8 mm


### Complementary

[Ue] rated operational voltage	250 V AC 50 Hz
[Ithe] conventional enclosed thermal current	10 A
[Ie] rated operational current	10 A
Connections - terminals	Screw terminals cable(s) 1.5...6 mm <sup>2</sup> rigid or stranded
Height	101 mm
Width	101 mm
Depth	101 mm
Net weight	0.471 kg
Colour	Body: grey (RAL 7035) Rotary handle: dark grey

### Environment

Standards	AS/NZS 3133
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

### Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>