

Product data sheet

Characteristics

FOS105T-GY

SWITCHED SOCKET FLUSH 15A EXTRA LOW VOLTAGE



Main

Range of product	Wilco
Colour	Grey
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	GY
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	15 A

Packing Units

Package 1 Weight	0.058 kg
Package 1 Height	26.000 mm
Package 1 width	38.000 mm
Package 1 Length	90.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.