

## Product data sheet

### Characteristics

# G10FMD15S-WE

## SWITCHED SOCKET MECHANISM DOUBLE POLE SHUTTER



### Main

Range of product	Series G10F
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Protection type	Fingersafe
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Depth	26 mm
Diameter	74 mm
Fixing center	64 mm
Number of poles	2

### Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

### Packing Units

Package 1 Weight	0.082 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>