

## Product data sheet

### Characteristics

# GV4APN04

## TeSys GV4 - extended rotary handle red - IP65



### Main

Range	TeSys
Product or component type	Rotary handle kit
Accessory / separate part category	Control accessory
Rotary handle mounting style	Extended
Handle colour	Red
Handle front plate colour	Yellow
Marking	OFF - Trip - ON
Rotary handle padlocking	1 to 3 padlocks Padlock in ON position Padlock in OFF position

### Complementary

Range compatibility	TeSys GV4 TeSys BV4
Mounting mode	Fixed
Mounting location	Door of enclosure
Locking options description	1 to 3 padlocks Ø 4 to Ø 8
Back/door distance	214...627 mm

### Environment

IP degree of protection	IP65
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	743 g
Package 1 Height	8.8 cm
Package 1 width	9 cm
Package 1 Length	45.9 cm
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Weight	9.209 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm
Unit Type of Package 3	P12
Number of Units in Package 3	20
Package 3 Weight	24.884 kg
Package 3 Height	50 cm
Package 3 width	80 cm
Package 3 Length	120 cm

## Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins