

## Product data sheet

### Characteristics

# GVAPR54

TeSys, Rotary handle, TeSys Deca-GV3-U, IP54, red handle, with trip indication



### Main

|                                   |                   |
|-----------------------------------|-------------------|
| Range                             | TeSys             |
| Device short name                 | GVAP              |
| Product or component type         | Rotary handle     |
| Accessory / separate part categor | Control accessory |
| Handle colour                     | Red               |
| Handle front plate colour         | Yellow            |
| Colour                            | Red<br>Yellow     |

### Complementary

|                              |   |
|------------------------------|---|
| Range compatibility          | TeSys TeSys GV2<br>TeSys TeSys GV3<br>TeSys TeSys Ultra |
| Rotary handle padlocking     | Padlock in OFF position                                 |
| Rotary handle mounting style | Direct  |
| Locking options description  | 1 to 3 padlocks   |
| Height                       | 43 mm   |
| Width                        | 60 mm   |
| Depth                        | 60 mm   |
| Net weight                   | 0.15 kg   |

### Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP54 |
|-------------------------|------|

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 6.7 cm   |
| Package 1 Width              | 9.0 cm   |
| Package 1 Length             | 13.5 cm  |
| Package 1 Weight             | 178.0 g  |
| Unit Type of Package 2       | S03      |
| Number of Units in Package 2 | 32       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 6.409 kg |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Compliant with Exemptions   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| RoHS exemption information | <a href="#">Yes</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End Of Life Information</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|