

## Product data sheet

### Characteristics

# IMT37413

Thorsman - TPP-13xM5S - cavity fixing - with screw - set of 5 - DIY



### Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TPP
Provided equipment	Screw
Mounting support	Board material - thickness: 10...35 mm
Thread type	M5
Screw diameter	5 mm
Screw length	65 mm
Drilling diameter	13 mm

### Complementary

Quantity per set	Set of 5
Net weight	0.0203 kg


### Environment

Material	Screw: steel electroplated Toggle: zinc Collar: zinc Spring: steel
Practical load capacity	Shear: 50 kg for 13 mm board 2.5) Pull-out load: 17 kg for 13 mm board 3) Shear: 80 kg for 2 x 13 mm board 2.5) Pull-out load: 34 kg for 2 x 13 mm board 3)
Thickness	0...47 Mm fixture 13 mm board 0...34 mm fixture 2 x 13 mm board
Type of packing	Plastic bag and cardboard with eurohole
Ambient air temperature for operation	-20...80 °C
Diameter	18 mm
Length	90 mm

### Packing Units

Package 1 Weight	0.109 kg
Package 1 Height	1.350 dm
Package 1 width	0.150 dm
Package 1 Length	0.930 dm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

---

RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---