

## Product data sheet

### Characteristics

# IMT37414

Thorsman installation material, cavity fixing, with screw, TPD-SK, set of 5, DIY



#### Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TPD
Provided equipment	Screw
Mounting support	Lightweight installation in board material - thickness: 9 mm
Screw diameter	4.5 mm
Screw length	35 mm
Size of screw head	8 mm
Shape of screw head	Cross slotted
Screwdriver shape	Pozidriv No 2

#### Complementary

Quantity per set	Set of 5
Net weight	0.0089 kg



#### Environment

Material	Screw: steel electro-galvanized Cavity fixing: zinc
Practical load capacity	Shear: 27 kg for 13 mm board 2.5) Pull-out load: 8 kg for 13 mm board 3)
Thickness	0...12 mm fixture
Environmental characteristic	Fire resistance
Type of packing	Plastic bag and cardboard with eurohole
Ambient air temperature for operation	-40...80 °C
Diameter	13 mm
Length	37 mm

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	1.5 cm
Package 1 Length	9.3 cm
Package 1 Weight	29.0 g

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>