

Product data sheet

Characteristics

IMT37419

Thorsman - TMX-4D - cavity fixing - with threaded screw - set of 5 - DIY



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TMX
Provided equipment	Threaded screw
Mounting support	High load installation in board material - thickness: 16...26 mm
Thread type	M4
Screw diameter	4 mm
Screw length	50 mm
Shape of screw head	Combi-head Cross slotted
Screwdriver shape	Philips
Drilling diameter	8 mm

Complementary

Quantity per set	Set of 5
Net weight	0.0093 kg




Environment

Material	Screw: steel electroplated Cavity fixing: sheet metal electroplated
Practical load capacity	Shear: 40 kg 2.5) Pull-out load: 16 kg 3)
Thickness	0...18 mm
Environmental characteristic	Fire resistance
Type of packing	Plastic bag and cardboard with eurohole
Ambient air temperature for operation	-40...80 °C
Diameter	14 mm
Length	62 mm

Packing Units

Package 1 Weight	0.009 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
