

## Product data sheet

### Characteristics

# IMT37419

Thorsman installation material, cavity fixing, with threaded screw, TMX-4D, set of 5, DIY



### Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TMX
Provided equipment	Threaded screw
Mounting support	High load installation in board material - thickness: 16...26 mm
Thread type	M4
Screw diameter	4 mm
Screw length	50 mm
Shape of screw head	Combi-head Cross slotted
Screwdriver shape	Philips
Drilling diameter	8 mm

### Complementary

Quantity per set	Set of 5
Net weight	0.0093 kg

### Environment

Material	Screw: steel electroplated Cavity fixing: sheet metal electroplated
Practical load capacity	Shear: 40 kg 2.5) Pull-out load: 16 kg 3)
Thickness	0...18 mm
Environmental characteristic	Fire resistance
Type of packing	Plastic bag and cardboard with eurohole
Ambient air temperature for operation	-40...80 °C
Diameter	14 mm
Length	62 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.4 cm
Package 1 Width	1.4 cm
Package 1 Length	6.2 cm
Package 1 Weight	9.0 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations