

## Product data sheet

### Characteristics

# IMT37489

Thorsman - double cable wing - without nail plug - dark grey - DIY - 2 pack



### Main

Range of product	Thorsman
Product or component type	Double cable wing
Provided equipment	Without nail plug
Device application	Cable installation two sides Conduit installation two sides
Colour tint	Dark grey
Type of packing	Plastic bag and cardboard with eurohole
Quantity per set	Set of 2

### Complementary

Type of installation	Indoor/outdoor
Number of cables	6 x 0...12 mm: both side
Practical load capacity	30 N
Material	Cable wing: PA (polyamide)
Height	23 mm
Width	20 mm
Depth	230 mm




### Environment

Ambient air temperature for operation	-20...60 °C
Environmental characteristic	Withstand extreme temperature High UV resistance Halogen free

### Packing Units

Package 1 Weight	0.027 kg
Package 1 Height	1.550 dm
Package 1 width	0.250 dm
Package 1 Length	1.460 dm

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>