

## Product data sheet

### Characteristics

# IMT37489

Thorsman - double cable wing - without nail plug - dark grey - DIY - 2 pack



### Main

Range of product	Thorsman
Product or component type	Double cable wing
Provided equipment	Without nail plug
Device application	Cable installation two sides Conduit installation two sides
Colour tint	Dark grey
Type of packing	Plastic bag and cardboard with eurohole
Quantity per set	Set of 2

### Complementary

Type of installation	Indoor/outdoor
Number of cables	6 x 0...12 mm: both side
Practical load capacity	30 N
Material	Cable wing: PA (polyamide)
Height	23 mm
Width	20 mm
Depth	230 mm

### Environment

Ambient air temperature for operation	-20...60 °C
Environmental characteristic	Withstand extreme temperature High UV resistance

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	45.0 g
Package 1 Height	32.0 cm
Package 1 Width	2.5 cm
Package 1 Length	15.0 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	1440
Package 2 Weight	93.312 kg
Package 2 Height	105.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	254.0 g
Package 3 Height	2.5 cm

Package 3 Width	45.0 cm
Package 3 Length	55.0 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>