

Product data sheet

Characteristics

IMT39082

Thorsman - TPH-10x67 - nail plug - with 72 mm screw - set of 20



Main

Range of product	Thorsman
Product or component type	Nail plug
Device short name	TPH
Provided equipment	Screw
Drilling diameter	10 mm
Minimum drilling depth	70 mm
Screw length	72 mm

Complementary

Colour tint	Green/black
Material	Screw: acid-proof stainless steel Plug: PA + TPR
Atmospheric-corrosivity category	C5-M
Practical load capacity	Pull-out load: 0.6 kN for low density concrete 500 and expanded clay 3) Shear: 0.7 kN for low density concrete 500 and expanded clay 2.5) Pull-out load: 0.8 kN for concrete C25 3) Shear: 1 kN for concrete C25 2.5)
Thickness	0...10 mm fixture
Ambient air temperature for operation	-20...60 °C
Diameter	10 mm
Length	67 mm

Environment

Quantity per set	Set of 20
------------------	-----------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------