

Product data sheet

Characteristics

IMT39082

Thorsman installation material, nail plug, with 72 mm screw, TPH-10x67, set of 20



Main

Range of product	Thorsman
Product or component type	Nail plug
Device short name	TPH
Provided equipment	Screw
Drilling diameter	10 mm
Minimum drilling depth	70 mm
Screw length	72 mm

Complementary

Colour tint	Green/black
Material	Screw: acid-proof stainless steel Plug: PA + TPR
Atmospheric-corrosivity category	C5-M
Practical load capacity	Pull-out load: 0.6 kN for low density concrete 500 and expanded clay 3) Shear: 0.7 kN for low density concrete 500 and expanded clay 2.5) Pull-out load: 0.8 kN for concrete C25 3) Shear: 1 kN for concrete C25 2.5)
Thickness	0...10 mm fixture
Ambient air temperature for operation	-20...60 °C
Diameter	10 mm
Length	67 mm

Environment

Quantity per set	Set of 20
------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.200 cm
Package 1 Width	10.600 cm
Package 1 Length	21.800 cm
Package 1 Weight	17.100 g
Unit Type of Package 2	CAR
Number of Units in Package 2	320
Package 2 Height	15.200 cm
Package 2 Width	29.800 cm
Package 2 Length	39.800 cm
Package 2 Weight	5.802 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	320
Package 3 Height	15.200 cm

Package 3 Width	29.800 cm
Package 3 Length	39.800 cm
Package 3 Weight	5.802 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------