

Product data sheet

Characteristics

IMT39086

Thorsman - TPH-10x110 - nail plug - with 115 mm screw - set of 20



Main

Range of product	Thorsman
Product or component type	Nail plug
Device short name	TPH
Provided equipment	Screw
Drilling diameter	10 mm
Minimum drilling depth	120 mm
Screw length	115 mm

Complementary

Colour tint	Green/black
Material	Screw: acid-proof stainless steel Plug: PA + TPR
Atmospheric-corrosivity category	C5-M
Practical load capacity	Pull-out load: 0.6 kN for low density concrete 500 and expanded clay 3) Pull-out load: 0.8 kN for concrete C25 3) Shear: 0.3 kN for low density concrete 500 and expanded clay 2.5) Shear: 0.3 kN for concrete C25 2.5)
Thickness	0...50 mm fixture
Ambient air temperature for operation	-20...60 °C
Diameter	10 mm
Length	110 mm

Environment

Quantity per set	Set of 20
------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	29 g
Package 1 Height	3.6 cm
Package 1 width	16 cm
Package 1 Length	22 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------