

Product data sheet

Characteristics

INS12100

installation trunking, OptiLine 50, 80 x 63 mm,
plastic, white, 2.5 m



Main

Range of product	OptiLine 50
Product or component type	Installation trunking
Colour tint	White (RAL 9010)
Quantity per set	10 m

Complementary

Compartment partitioning	1 compartment
Trunking dimension	80 x 63 mm
Trunking material	Plastic
Front opening size	50 mm
Fixing mode	Screw-fixed
Material	PC/ABS
Length	2500 mm
Height	80 mm
Width	63 mm


Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	6.3 cm
Package 1 Length	250 cm
Package 1 Weight	1 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------