

Product data sheet

Characteristics

INS12101

OptiLine 50, internal corner, 80 x 63 mm, PC/
ABS, white



Main

Product or component type	Internal corner
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	80 x 63 mm
Trunking material	Aluminium Plastic
Material	PC/ABS
Length	115 mm
Height	85 mm
Width	115 mm

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	16.3 cm
Package 1 Length	16.4 cm
Package 1 Weight	84 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
