

Product data sheet

Characteristics

INS12104

OptiLine 50, stop end, 80 x 63 mm, PC/ABS, white



Main

Product or component type	Stop end
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	80 x 63 mm
Trunking material	Plastic Aluminium
Fixing mode	Screw-fixed
Material	PC/ABS
Length	65 mm
Height	84 mm
Width	30 mm



Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	3 cm
Package 1 Length	6.5 cm
Package 1 Weight	30 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
