

## Product data sheet

### Characteristics

# INS12106

OptiLine 50 - joint cover piece - 80 x 63 mm -  
PC/ABS - white



#### Main

Product or component type	Joint cover piece
Quantity per set	1 piece
Colour tint	White (RAL 9010)

#### Complementary

Trunking dimension	80 x 63 mm
Trunking material	Plastic Aluminium
Material	PC/ABS
Length	90 mm
Height	84 mm
Width	65 mm

#### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	8.9 cm
Package 1 Length	14.8 cm
Package 1 Weight	24 g

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

---

RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---