

Product data sheet

Characteristics

INS12106

OptiLine 50 - joint cover piece - 80 x 63 mm - PC/ABS - white



Main

Product or component type	Joint cover piece
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	80 x 63 mm
Trunking material	Plastic Aluminium
Material	PC/ABS
Length	90 mm
Height	84 mm
Width	65 mm




Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	24 g
Package 1 Height	3.9 cm
Package 1 width	8.9 cm
Package 1 Length	14.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)

Contractual warranty

Warranty

18 months
