

Product data sheet

Characteristics

INS12200

OptiLine 50 - installation trunking - 100 x 63 mm - plastic - white - 2.5 m



Main

Range of product	OptiLine 50
Product or component type	Installation trunking
Colour tint	White (RAL 9010)
Quantity per set	10 m

Complementary

Compartment partitioning	1 compartment
Trunking dimension	100 x 63 mm
Trunking material	Plastic
Front opening size	50 mm
Fixing mode	Screw-fixed
Material	PC/ABS
Length	2500 mm
Height	100 mm
Width	63 mm

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1504 g
Package 1 Height	100 mm
Package 1 width	63 mm
Package 1 Length	2500 mm
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	7.219 kg
Package 2 Height	7.8 cm
Package 2 width	26.3 cm
Package 2 Length	253.3 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	320
Package 3 Weight	231.008 kg

Package 3 Height	76.4 cm
Package 3 width	120 cm
Package 3 Length	262 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------