

Product data sheet

Characteristics

INS12202

OptiLine 50 - external corner - 100 x 63 mm -
PC/ABS - white



Main

Product or component type	External corner
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	100 x 63 mm
Trunking material	Plastic Aluminium
Material	PC/ABS
Length	115 mm
Height	105 mm
Width	115 mm




Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	98 g
Package 1 Height	9.6 cm
Package 1 width	12.8 cm
Package 1 Length	16 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
