

Product data sheet

Characteristics

INS12205

OptiLine 50, wall/ceiling frame, 100 x 63 mm, PC/ABS, white



Main

Product or component type	Wall/ceiling frame
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	100 x 63 mm
Trunking material	Plastic Aluminium
Fixing mode	Screw-fixed
Material	PC/ABS
Length	88 mm
Height	150 mm
Width	225 mm



Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	11 cm
Package 1 Length	17.6 cm
Package 1 Weight	34 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
