

Product data sheet

Characteristics

INS12206

OptiLine 50 - joint cover piece - 100 x 63 mm - PC/ABS - white



Main

Product or component type	Joint cover piece
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	100 x 63 mm
Trunking material	Plastic Aluminium
Material	PC/ABS
Length	90 mm
Height	104 mm
Width	65 mm




Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	26 g
Package 1 Height	3.9 cm
Package 1 width	10.5 cm
Package 1 Length	14.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
