

Product data sheet

Characteristics

INS12207

T-piece, OptiLine 50, 100 x 63 mm, PC/ABS, white



Main

Product or component type	T-piece
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	100 x 63 mm
Trunking material	Aluminium Plastic
CMS inst product add info	For vertical trunking 100 and horizontal trunking 100, 120, 140
Material	PC/ABS
Length	121 mm
Height	52 mm
Width	63 mm

Environment



Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	12.5 cm
Package 1 Length	16.7 cm
Package 1 Weight	30 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------