

Product data sheet

Characteristics

INS12207

OptiLine 50 - T-piece - 100 x 63 mm - PC/ABS - white



Main

Product or component type	T-piece
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	100 x 63 mm
Trunking material	Aluminium Plastic
CMS inst product add info	For vertical trunking 100 and horizontal trunking 100, 120, 140
Material	PC/ABS
Length	121 mm
Height	52 mm
Width	63 mm



Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	30 g
Package 1 Height	5.1 cm
Package 1 width	12.5 cm
Package 1 Length	16.7 cm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
