

Product data sheet

Characteristics

INS12301

OptiLine 50 - internal corner - 120 x 63 mm -
PC/ABS - white



Main

| | |
|---------------------------|------------------|
| Product or component type | Internal corner |
| Quantity per set | 1 piece |
| Colour tint | White (RAL 9010) |

Complementary

| | |
|---------------------------|----------------------|
| Trunking dimension | 120 x 63 mm |
| Trunking material | Aluminium Plastic |
| CMS inst product add info | Adjustable |
| Material | PC/ABS |
| Length | 150 mm |
| Height | 129 mm |
| Width | 150 mm |




Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...60 °C |
| IP degree of protection | IP40 |
| IK degree of protection | IK07 |

Packing Units

| | |
|------------------|------------|
| Package 1 Weight | 1.000 kg |
| Package 1 Height | 129.000 mm |
| Package 1 width | 150.000 mm |
| Package 1 Length | 150.000 mm |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| RECh Regulation |  RECh Declaration |
| RECh free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information |  Yes |

| | |
|--------------------------|---|
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|
