

## Product data sheet

### Characteristics

# INS12302

OptiLine 50 - external corner - 120 x 63 mm -  
PC/ABS - white



### Main

Product or component type	External corner
Quantity per set	1 piece
Colour tint	White (RAL 9010)

### Complementary

Trunking dimension	120 x 63 mm
Trunking material	Aluminium Plastic
CMS inst product add info	Adjustable
Material	PC/ABS
Length	153 mm
Height	129 mm
Width	153 mm



### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	145 g
Package 1 Height	12.9 cm
Package 1 width	15.3 cm
Package 1 Length	15.3 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

---

RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---