

Product data sheet

Characteristics

INS12304

stop end, OptiLine 50, 120 x 63 mm, PC/ABS, white



Main

Product or component type	Stop end
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	120 x 63 mm
Trunking material	Aluminium Plastic
Fixing mode	Screw-fixed
Material	PC/ABS
Length	65 mm
Height	124 mm
Width	30 mm

Environment



Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	6.5 cm
Package 1 Length	12.4 cm
Package 1 Weight	40 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------
