

Product data sheet

Characteristics

INS12305

OptiLine 50 - wall frame - 120 x 63 mm - PC/
ABS - white



Main

Product or component type	Wall frame
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	120 x 63 mm
Trunking material	Aluminium Plastic
Fixing mode	Screw-fixed
Material	PC/ABS
Length	113 mm
Height	170 mm
Width	225 mm



Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Package 1 Weight	1.000 kg
Package 1 Height	170.000 mm
Package 1 width	22.500 mm
Package 1 Length	113.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
