

## Product data sheet

### Characteristics

# INS12306

OptiLine 50 - joint cover piece - 120 x 63 mm -  
PC/ABS - white



#### Main

Product or component type	Joint cover piece
Quantity per set	1 piece
Colour tint	White (RAL 9010)

#### Complementary

Trunking dimension	120 x 63 mm
Trunking material	Aluminium Plastic
Material	PC/ABS
Length	90 mm
Height	124 mm
Width	65 mm




#### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	25 g
Package 1 Height	12.4 cm
Package 1 width	6.5 cm
Package 1 Length	9 cm

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---