

## Product data sheet

### Characteristics

# INS12404

OptiLine 50, stop end, 140 x 63 mm, PC/ABS, white



### Main

Product or component type	Stop end
Quantity per set	1 piece
Colour tint	White (RAL 9010)

### Complementary

Trunking dimension	140 x 63 mm
Fixing mode	Screw-fixed
Material	PC/ABS
Length	65 mm
Height	144 mm
Width	30 mm


### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	6.5 cm
Package 1 Length	14.3 cm
Package 1 Weight	42 g

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 <a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---