

Product data sheet

Characteristics

INS12405

OptiLine 50 - wall frame - 140 x 63 mm - PC/
ABS - white



Main

Product or component type	Wall frame
Quantity per set	1 piece
Colour tint	White (RAL 9010)

Complementary

Trunking dimension	140 x 63 mm
Trunking material	Aluminium Plastic
Fixing mode	Screw-fixed
Material	PC/ABS
Length	113 mm
Height	190 mm
Width	225 mm

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------