

Product data sheet

Characteristics

INS12910

OptiLine 50, spacer, 120 x 63 mm, PC/ABS, green



Main

Product or component type	Spacer
Quantity per set	1 piece
Colour tint	Green

Complementary

Trunking dimension	120 x 63 mm 140 x 63 mm
Trunking material	Plastic Aluminium
Material	PC/ABS
Length	30 mm
Height	10 mm
Width	12 mm



Environment




Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	1.2 cm
Package 1 Length	3 cm
Package 1 Weight	8 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------