

## Product data sheet

### Characteristics

# INS12911

OptiLine 50 - joint cover piece - 120 x 63 mm -  
PC/ABS - white



### Main

Product or component type	Joint cover piece
Quantity per set	1 piece
Colour tint	White (RAL 9010)

### Complementary

Trunking dimension	120 x 63 mm 140 x 63 mm
Trunking material	Aluminium Plastic
Material	PC/ABS
Length	54 mm
Height	27 mm
Width	65 mm



### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	10 g
Package 1 Height	2.9 cm
Package 1 width	7.2 cm
Package 1 Length	15 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

---

RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---