

## Product data sheet

### Characteristics

# INS43402

OptiLine 50 - pole - free-standing - one sided - empty - anodized - Australian



### Main

Range	OptiLine
Product name	OptiLine 50
Product type	Pole
Type of pole	One-sided
Configuration	Empty
Additional information	Flexible conduit 2000 mm
Colour	Natural
Quantity package 1 / unit	Set of 1

### Complementary

Pole/post surface finish	Anodized
Fixing mode	Free-standing
Device composition	Front cover Floor fixing Stop end Earth terminal Earth clamp Mounting instruction Flexible conduit 2000 mm Strain relief Earth cable
Product material	Aluminium conforming to EN-AW-6063 PC/ABS conforming to UL 94 HB
Marking	CE
Height	2150 mm
Width	68 mm

### Environment

Standards	EN 50085-1:2005 IEC 1084-2-4 EN 60598-2-2 73/23/EEC 93/68/EEC
Directives	2014/35/EU - low voltage directive
Operating temperature	-15...60 °C
IP degree of protection	IP30

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	5.91 kg
Package 1 Height	6.8 cm
Package 1 width	8.9 cm
Package 1 Length	215 cm

## Offer Sustainability

EU RoHS Directive

Not applicable, out of EU RoHS legal scope