

Product data sheet

Characteristics

INS43406

OptiLine 50 - pole - tension-mounted - one sided - empty - anodized - Australian



Main

| | |
|---------------------------|--|
| Range | OptiLine |
| Product name | OptiLine 50 |
| Product type | Pole |
| Type of pole | One-sided |
| Configuration | Empty |
| Additional information | Adjustability of ceiling fixing 400 mm |
| Colour | Natural |
| Quantity package 1 / unit | Set of 1 |

Complementary

| | |
|--------------------------|---|
| Pole/post surface finish | Anodized |
| Fixing mode | Tension-mounted |
| Device composition | Front cover Floor fixing Floor fixing plate Ceiling fixing Ceiling frame Stop end Earth terminal Earth clamp Mounting instruction Strain relief Earth cable |
| Product material | Aluminium conforming to EN-AW-6063 PC/ABS conforming to UL 94 HB |
| Marking | CE |
| Height | 2700...3100 mm |
| Width | 68 mm |

Environment

| | |
|-------------------------|---|
| Standards | EN 50085-1:2005 IEC 1084-2-4 EN 60598-2-2 73/23/EEC 93/68/EEC |
| Directives | 2014/35/EU - low voltage directive |
| Operating temperature | -15...60 °C |
| IP degree of protection | IP30 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 6.31 kg |
| Package 1 Height | 6.8 cm |
| Package 1 Width | 8.9 cm |
| Package 1 Length | 270 cm |

| | |
|------------------------------|-----------|
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 1 |
| Package 2 Weight | 7.285 kg |
| Package 2 Height | 12.7 cm |
| Package 2 Width | 15.5 cm |
| Package 2 Length | 274 cm |
| Unit Type of Package 3 | PAL |
| Number of Units in Package 3 | 28 |
| Package 3 Weight | 206.78 kg |
| Package 3 Height | 77 cm |
| Package 3 Width | 120 cm |
| Package 3 Length | 340 cm |

Offer Sustainability

| | |
|-------------------|--|
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
|-------------------|--|