

## Product data sheet

### Characteristics

# INS43412

OptiLine 50 - pole - free-standing - two sided - empty - anodized - Australian



### Main

Range	OptiLine
Product name	OptiLine 50
Product type	Pole
Type of pole	Two-sided
Configuration	Empty
Additional information	Flexible conduit 2000 mm
Colour	Natural
Quantity package 1 / unit	Set of 1

### Complementary

Pole/post surface finish	Anodized
Fixing mode	Free-standing
Device composition	Front cover Floor fixing Stop end Earth terminal Earth clamp Mounting instruction Flexible conduit 2000 mm Strain relief Earth cable
Product material	Aluminium conforming to EN-AW-6063 PC/ABS conforming to UL 94 HB
Marking	CE
Height	2150 mm
Width	116 mm

### Environment

Standards	EN 50085-1:2005 IEC 1084-2-4 EN 60598-2-2 73/23/EEC 93/68/EEC
Directives	2014/35/EU - low voltage directive
Operating temperature	-15...60 °C
IP degree of protection	IP30

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	6.75 kg
Package 1 Height	11.6 cm
Package 1 Width	9 cm
Package 1 Length	215 cm
Unit Type of Package 2	CAR

Number of Units in Package 2	1
Package 2 Weight	7.725 kg
Package 2 Height	15.9 cm
Package 2 Width	27.7 cm
Package 2 Length	219 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	20
Package 3 Weight	219.1 kg
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	260 cm

## Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--