

Product data sheet

Characteristics

INS43512

OptiLine, Optiline 50 - post - 2-sided - empty - anodized - Australian

Main

Range	OptiLine
Product name	OptiLine 50
Product type	Post
Type of post	Two-sided
Configuration	Empty
Colour tint	Aluminium
Quantity package 1 / unit	Set of 1
Cover type	2 closed cover cover 50 mm in plastic anodised

Complementary

Pole/post surface finish	Anodized
Device composition	Front cover Stop end Earth clamp Mounting instruction Floor fixing Gasket ring Strain relief Earth cable
Fixing mode	By screws
Product material	Aluminium grey RAL 9007 conforming to EN-AW-6063 PC/ABS grey RAL 7043 conforming to UL 94 HB
Marking	CE
Height	602 mm
Width	156 mm
Adjustment	Fixed:
Useful cross section	7904 mm ²
Compartment partitioning	2 compartments

Environment

Standards	EN 50085-1:2005 73/23/EEC 93/68/EEC
Directives	2014/35/EU - low voltage directive
Operating temperature	-15...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.6 cm
Package 1 Width	12.5 cm
Package 1 Length	60.2 cm
Package 1 Weight	1.95 kg

Offer Sustainability

EU RoHS Directive

Not applicable, out of EU RoHS legal scope