

Product data sheet

Characteristics

INS43522

Optiline 50 - post - 4-sided - empty - anodized - Australian



Main

Range	OptiLine
Product name	OptiLine 50
Product type	Post
Type of post	Four-sided
Configuration	Empty
Quantity package 1 / unit	Set of 1
Cover type	4 50 mm in plastic untreated
Cover plate colour tint	Anthracite (RAL 7043)

Complementary

Pole/post surface finish	Anodized
Device composition	Front cover Stop end Earth clamp Mounting instruction Floor fixing Gasket ring Strain relief Earth cable
Fixing mode	By screws
Product material	Aluminium grey RAL 9007 conforming to EN-AW-6063 PC/ABS grey RAL 7043 conforming to UL 94 HB
Marking	CE
Height	592 mm
Width	200 mm
Adjustment	Fixed:
Useful cross section	13966 mm ²
Compartment partitioning	4 compartments

Environment

Standards	EN 50085-1:2005 73/23/EEC 93/68/EEC
Directives	2014/35/EU - low voltage directive
Product certifications	Low voltage directive 73/23/EEC
Operating temperature	-15...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.18 kg
Package 1 Height	20 cm
Package 1 width	18 cm
Package 1 Length	59.2 cm