

Product data sheet

Characteristics

INS43523

Post, OptiLine 50, 4-sided, empty, white, Australian

Main

Range	OptiLine
Product name	OptiLine 50
Product type	Post
Type of post	Four-sided
Configuration	Empty
Colour tint	White (RAL 9010)
Quantity package 1 / unit	Set of 1
Cover type	4 closed cover cover 50 mm in plastic coated

Complementary

Pole/post surface finish	Powder coated
Device composition	Front cover Stop end Earth clamp Mounting instruction Floor fixing Gasket ring Strain relief Earth cable
Fixing mode	By screws
Product material	Aluminium grey RAL 9007 conforming to EN-AW-6063 PC/ABS white RAL 9010 conforming to UL 94 HB
Marking	CE
Height	592 mm
Width	200 mm
Adjustment	Fixed:
Useful cross section	13966 mm ²
Compartment partitioning	4 compartments

Environment

Standards	EN 50085-1:2005 73/23/EEC 93/68/EEC
Directives	2014/35/EU - low voltage directive
Product certifications	low voltage directive 73/23/EEC
Operating temperature	-15...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20 cm
Package 1 Width	18 cm
Package 1 Length	59.2 cm
Package 1 Weight	4.18 kg

Offer Sustainability

EU RoHS Directive

Not applicable, out of EU RoHS legal scope
