

Product data sheet

Characteristics

INS43630

OptiLine 50, OptiLine 50 - service box - pop-up
 - 1x2 outlet, 2xRJ45 30 Mech/Keystone - AU



Main

Range	OptiLine 50
Range of product	OptiLine 50
Product or component type	Service box
Additional information	3 m power cable
Type of service box	Pop-up
Device presentation	Complete product
Colour	Aluminium
Outlet standard	Australian

Complementary

Mounting mode	Flush-mounted
Number of socket	1
Number of data socket outlets	2 x RJ45 blind
Product material	Aluminium anodized Aluminium powder coated Zinc powder coated
Diameter	112 mm




Environment

Operating temperature	-15...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.4 cm
Package 1 Width	17.3 cm
Package 1 Length	63.6 cm
Package 1 Weight	1.69 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.