

Product data sheet

Characteristics

INS43630

OptiLine 50 - service box - pop-up - 1x2 outlet,
2xRJ45 30 Mech/Keystone - AU



Main

Range	OptiLine 50
Range of product	OptiLine 50
Product type	Service box
Additional information	3 m power cable
Type of service box	Pop-up
Configuration	Pre-wired
Colour	Natural
Outlet standard	Australian
Quantity package 1 / unit	1 piece

Complementary

Interface	Keystone 30-mech
Number of socket	1 - earthed
Number of data socket outlets	2 x RJ45 blind
Product material	Aluminium anodized Aluminium powder coated Zinc powder coated
Diameter	112 mm




Environment

Operating temperature	-15...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.69 kg
Package 1 Height	15.4 cm
Package 1 width	17.3 cm
Package 1 Length	63.6 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	18
Package 2 Weight	43.42 kg
Package 2 Height	63 cm
Package 2 width	80 cm
Package 2 Length	120 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration