

## Product data sheet

### Characteristics

# INS51215

## lid for 12 modules steel box, OptiLine 50, gunmetal steel

### Main

Product type	Lid
Cabling installation system	Floor outlet box
Type of floor	Hollow core floor Raised floor In-cavity floor
Floor box shape	Rectangular
Colour	Gun metal
Quantity package 1 / unit	Set of 1

### Complementary

Suitable for	For 12 modules steel box
Fixing mode	Self-adhesive tape
Number of modules	12 modules
Product material	Aluminium alloy
Height	21 mm
Width	255 mm
Depth	378 mm

### Environment

IK degree of protection	IK07
IP degree of protection	IP20
Maximum load	10000 N

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	31.4 cm
Package 1 Length	41.4 cm
Package 1 Weight	1.8 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.